

# Eaton NZMH3-AEF400-NA

Catalog Number: NZMH3-AEF400-NA

Eaton Series NZM complete molded case circuit breaker, NZM3-frame, NZMH3, Thermal-magnetic trip, Three-pole, 400A, 690 Vac, 100 kAIC at 480 Vac, Distribution circuit protection, 400-400A, 800-4400A delayed, Front screw, 400-400A



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Series NZM complete molded case circuit breaker	NZMH3-AEF400-NA
	<b>EAN</b>
	4015082692865
<b>Product Length/Depth</b>	<b>Product Height</b>
5.51 in	6.53 in
<b>Product Width</b>	<b>Product Weight</b>
6.53 in	5.5 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## defaultTaxonomyAttributeLabel

### Amperage Rating

400 A

### Voltage rating

690 V AC

### Trip Type

Thermal-magnetic

### Circuit breaker type

NZMH3

### Frame

NZM3

### Class

Distribution circuit protection

### Accessories

Rocker lever, motor drive

### Adjustment range short-circuit release

800-4400A delayed

### Setting Range OI Protector

400-400A

### Short-circuit breaking capacity

150 kAIC

### Interrupt rating

100 kAIC at 480 Vac

### Connection

Front screw

### Overload range

400-400A

### Number of poles

Three-pole

## Resources

### Specifications and datasheets

[Product Data Sheet - NZMH3-AEF400-NA](#)

[Eaton Specification Sheet - NZMH3-AEF400-NA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)