

Eaton NZMN2-A63-BT-NA

Catalog Number: NZMN2-A63-BT-NA

Eaton Series NZM complete molded case circuit breaker, NZM2-frame, NZMN2, Thermal-magnetic trip, Three-pole, 63A, 690 Vac, 750 Vdc, 50 kAIC, Box, Distribution circuit protection, 50-63A, 380-630A delayed, Front frame clamp, 50-63A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series NZM complete molded case circuit breaker	NZMN2-A63-BT-NA
	EAN
	4015081074372
Product Length/Depth	Product Height
4.05 in	7.24 in
Product Width	Product Weight
4.13 in	4.1 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed

defaultTaxonomyAttributeLabel

Amperage Rating

63 A

Voltage rating

690 Vac, 750 Vdc

Trip Type

Thermal-magnetic

Circuit breaker type

NZMN2

Terminals

Box

Frame

NZM2

Class

Distribution circuit protection

Accessories

Rocker lever, motor drive

Adjustment range short-circuit release

380-630A delayed

Setting Range OI Protector

50-63A

Short-circuit breaking capacity

50 kAIC

Interrupt rating

50 kAIC

Connection

Front frame clamp

Overload range

50-63A

Number of poles

Three-pole

Resources

Application notes

[Power Xpert Protection Manager x64](#)

Specifications and datasheets

[Product Data Sheet - NZMN2-A63-BT-NA](#)

[Eaton Specification Sheet - NZMN2-A63-BT-NA](#)

White papers

[Intelligent power starts with accurate, actionable data](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)