

Eaton NZMN3-VE400-NA

Catalog Number: NZMN3-VE400-NA

Eaton Series NZM complete molded case circuit breaker, NZM3-frame, NZMN3, Thermal-magnetic trip, Three-pole, 400A, 690 Vac, 50 kAIC at 415 Vac, 42 kAIC at 480 Vac, Selective and gen. protect., 200-400A, Front screw, 200-400A



General specifications

Product Name	Catalog Number
Eaton Series NZM complete molded case circuit breaker	NZMN3-VE400-NA
	EAN
	4015082693336
Product Length/Depth	Product Height
6.535 in	5.512 in
Product Width	Product Weight
5.512 in	5.5 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

400 A

Voltage rating

690 V AC

Trip Type

Thermal-magnetic

Circuit breaker type

NZMN3

Frame

NZM3

Class

Selective and generator protection

Accessories

Rocker lever, motor drive

Adjustment range short-circuit release

400-4000A delayed, 800-4400A delayed

Setting Range OI Protector

200-400A

Short-circuit breaking capacity

50 kAIC

Interrupt rating

50 kAIC at 415 Vac

42 kAIC at 480 Vac

Connection

Front screw

Overload range

200-400A

Number of poles

Three-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - NZMN3-VE400-NA](#)

[Product Data Sheet - NZMN3-VE400-NA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)