

Eaton NZM2-XR24-30DC

Catalog Number: NZM2-XR24-30DC

Eaton molded case circuit breaker accessory box terminal, Remote operator, 24-30 Vdc, NZM2, Series NZM, 24-30 Vdc

General specifications



Product Name

Eaton molded case circuit breaker
accessory box terminal

Catalog Number

NZM2-XR24-30DC

EAN

4015082598365

Product Length/Depth

1.378 in

Product Height

1.378 in

Product Width

1.378 in

Product Weight

3.995 lb

Warranty

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Type

Remote operator

Voltage rating

24-30 Vdc

Series

Series NZM

Used with

NZM2

Rated control supply voltage

24-30 Vdc

Catalogs

[Compact circuit-breakers and switch-disconnectors up to 1600 A](#)

Multimedia

[Flex shaft handle installation tutorial](#)

Specifications and datasheets

[Eaton Specification Sheet - NZM2-XR24-30DC](#)

[Product Data Sheet - NZM2-XR24-30DC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)