

Eaton NZMB2-AF200-BT-NA

Catalog Number: NZMB2-AF200-BT-NA

MCCB NZM, NZM2 TM and Elec. Breakers, Circuit Breaker, 200-200A OL Prot. Rng, Frame clamp, front, Three-pole, 200A Perm. Current, 25 kA, 200-200A Set. Rng OL Prot., 1200-2000A Undelayed Adj. Rng., Rocker lever, motor drive optional

General specifications



Photo is representative

Product Name

Eaton Series NZM complete molded case circuit breaker

Catalog Number

NZMB2-AF200-BT-NA

EAN

4015081072941

Product Length/Depth

5.51 in

Product Height

5.86 in

Product Width

5.86 in

Product Weight

5.17 lb

Warranty

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

defaultTaxonomyAttributeLabel

Amperage Rating

200 A

Voltage rating

440 Vac

Trip Type

Fixed thermal, adjustable magnetic

Circuit breaker type

NZMB2

Terminals

Box

Frame

NZM2

Class

Distribution circuit protection

Accessories

Rocker lever, motor drive

Adjustment range short-circuit release

1200-2000A delayed

Setting Range OI Protector

200-200A

Short-circuit breaking capacity

25 kAIC

Interrupt rating

25 kAIC

Connection

Front frame clamp

Overload range

200-200A

Number of poles

Three-pole

Resources

Specifications and datasheets

[Product Data Sheet - NZMB2-AF200-BT-NA](#)

[Eaton Specification Sheet - NZMB2-AF200-BT-NA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)