

Eaton NZMB2-A50-BT-NA

Catalog Number: NZMB2-A50-BT-NA

Eaton Series NZM complete molded case circuit breaker, NZM2-frame, NZMB2, Fixed thermal, adj. magnetic trip, 320-400A, Three-pole, 50A, 440 Vac, 25 kAIC, Box, Distribution circuit protect., 40-50A, Front frame clamp, 40-50A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series NZM complete molded case circuit breaker	NZMB2-A50-BT-NA
	EAN
	4015081074242
Product Length/Depth	Product Height
4.05 in	7.24 in
Product Width	Product Weight
4.13 in	4.1 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

50 A

Voltage rating

440 Vac

Trip Type

Fixed thermal, adjustable magnetic

Circuit breaker type

NZMB2

Terminals

Box

Frame

NZM2

Class

Distribution circuit protection

Accessories

Rocker lever, motor drive

Adjustment range short-circuit release

300-500A delayed

Setting Range OI Protector

40-50A

Short-circuit breaking capacity

25 kAIC

Interrupt rating

25 kAIC

Connection

Front frame clamp

Overload range

40-50A

Number of poles

Three-pole

Trip rating

320-400 A

Resources

Application notes

[Power Xpert Protection Manager x64](#)

Specifications and datasheets

[Eaton Specification Sheet - NZMB2-A50-BT-NA](#)

[Product Data Sheet - NZMB2-A50-BT-NA](#)

White papers

[Intelligent power starts with accurate, actionable data](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)