Eaton NZMH2-AF150-BT-NA

Catalog Number: NZMH2-AF150-BT-NA

Eaton Series NZM complete molded case circuit breaker, NZM2-frame, NZMH2, Adj. thermal, fixed magnetic trip, 960-1600A delayed, Three-pole, 150A, 690 Vac, 750 Vdc, 85-150 kAIC, Box, Distribution circuit protect., Front frame clamp

General specifications



Photo is representative

Product Name

Eaton Series NZM complete molded

case circuit breaker

Catalog Number

NZMH2-AF150-BT-NA

EAN

4015081074716

Product Length/Depth

5.9 in

4.1 in

Product Height

Product Weight

7.7 in

Product Width

4.1 lb

Warranty Compliances

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.



defaultTaxonomyAttributeLabel

Amperage Rating

150 A

Voltage rating

690 Vac, 750 Vdc

Trip Type

Adjustable thermal, fixed magnetic

Circuit breaker type

NZMH2

Terminals

Box

Frame

NZM2

Class

Distribution circuit protection

Accessories

Rocker lever, motor drive

Setting Range OI Protector

150-150A

Short-circuit breaking capacity

150 kAIC

Interrupt rating

85-150 kAIC

Connection

Front frame clamp

Overload range

150-150A

Number of poles

Three-pole

Trip rating

960-1600 A delayed

Resources

Specifications and datasheets

Eaton Specification Sheet - NZMH2-AF150-BT-NA

Product Data Sheet - NZMH2-AF150-BT-NA



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia