

Eaton NZMB2-AF50-BT-NA

Catalog Number: NZMB2-AF50-BT-NA

Eaton Series NZM complete molded case circuit breaker, NZM2-frame, NZMB2, Fixed thermal, adjustable magnetic trip, Three-pole, 50A, 440 Vac, 25 kAIC, Box, Distribution circuit protection, 50-50A, 300-500A delayed, Front frame clamp, 50-50A

General specifications



Photo is representative

Product Name

Eaton Series NZM complete molded case circuit breaker

Catalog Number

NZMB2-AF50-BT-NA

EAN

4015081072842

Product Length/Depth

4.05 in

Product Height

7.24 in

Product Width

4.13 in

Product Weight

4.1 lb

Warranty

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

defaultTaxonomyAttributeLabel

Amperage Rating

50 A

Voltage rating

440 Vac

Trip Type

Fixed thermal, adjustable magnetic

Circuit breaker type

NZMB2

Terminals

Box

Frame

NZM2

Class

Distribution circuit protection

Accessories

Rocker lever, motor drive

Adjustment range short-circuit release

300-500A delayed

Setting Range OI Protector

50-50A

Short-circuit breaking capacity

25 kAIC

Interrupt rating

25 kAIC

Connection

Front frame clamp

Overload range

50-50A

Number of poles

Three-pole

Resources

Specifications and datasheets

[Product Data Sheet - NZMB2-AF50-BT-NA](#)

[Eaton Specification Sheet - NZMB2-AF50-BT-NA](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)