

Eaton NZM2-XR208-240AC

Catalog Number: NZM2-XR208-240AC

Eaton molded case circuit breaker accessory box terminal, Remote operator, 208-240 V, NZM2, Series NZM, 208-240 V

General specifications



Photo is representative

Product Name	Catalog Number
Eaton molded case circuit breaker accessory box terminal	NZM2-XR208-240AC
	EAN
	4015082598327

Product Length/Depth	Product Height
1.378 in	1.378 in

Product Width	Product Weight
1.378 in	4.041 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Type

Remote operator

Voltage rating

208-240V

Series

Series NZM

Used with

NZM2

Rated control supply voltage

208-240 V

Multimedia

[Flex shaft handle installation tutorial](#)

Specifications and datasheets

[Product Data Sheet - NZM2-XR208-240AC](#)

[Eaton Specification Sheet - NZM2-XR208-240AC](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)