

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

WSL CHOICE

LED SLIM WALL PACK 3 CCT AND 3 POWER SELECTABLE INTEGRATED PHOTOCELL

ORDERING INFORMATION

Order code: 69723
Model number: WSL-PS60-Q-3C-BR/CHOICE
UPC: 069549029446
Case quantity: 1
DLC unique ID: in process

PHYSICAL DATA

Finish: Bronze
Housing material: Die-cast aluminum
Lens material: Prismatic tempered glass

PERFORMANCE DATA

Watts (W): 30/40/60
Volts (V AC): 120-347
Color temperature (K):¹ 3 000/4 000/5 000
Lumen output (lm):² 4 200/5 600/8 400
Efficacy (lm/W): 140
CRI: 80+
Life L70 (h):³ 50 000
THD (%): 20
IP rating: IP65
IK rating: IK08
Dimming: 0-10 V
B.U.G. rating: B1 U3 G3
Power factor: 0.99
Photocell: Yes
Surge protection (kV): 6
Operating temp. range: -40°C to 40°C (-40°F to 104°F)

¹ Typical colour temperature range: +/- 5 %.
² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

LUMEN SPECIFICATION TABLE

Watts (W)	3 000 K		4 000 K		5 000 K	
	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
30	4 283	136	4 395	142	4 516	143
40	5 469	133	5 698	141	5 801	140
60	7 672	131	7 872	137	7 908	133

DEFAULT PROGRAMMING
60 W / 4 000 K

This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



Bronze



IK08




ICES 005



ACCESSORY (order separately)

Order code	Type
69725	Wireguard




COMPATIBLE DIMMERS¹

Brand	Model
Lutron	NTSTV-DV, NFTV, DDTV-WH
Leviton	DS710, IP710
Legrand	H4FBL3PW

Dimming range: 0%-100%

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

DIMENSIONS AND WEIGHTS




A in. (mm)	13.82" (351)
B in. (mm)	8.88" (2263)
C in. (mm)	4.48" (114)
Net weight (lbs)	9.1

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

PHOTOMETRIC DATA¹

69723 • WSL-PS60-Q-3C-BR/CHOICE • 60 W • 4 000 K • 8 312 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 395.3	16.8
0-40	2 495.0	30
0-60	5 160.6	62.1
60-90	2 569.9	30.9
70-100	1 618.9	19.5
90-120	423.2	5.1
0-90	7 730.5	93
90-180	581.6	7
0-180	8 312.1	100

Illuminance at a distance

Center beam fc		Beam width	
1.7'	582 fc	2.2'	3.5'
3.3'	154 fc	4.3'	6.8'
5.0'	67.2 fc	6.5'	10.3'
6.7'	37.4 fc	8.8'	13.8'
8.3'	24.4 fc	10.9'	17.1'
10.0'	16.8 fc	13.1'	20.6'

Vert. spread: 66.4°
Horiz. spread: 91.7°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.