

Eaton SVX040A1-4A1N1

Catalog Number: SVX040A1-4A1N1

Eaton SVX adjustable frequency drive, 40HP, NEMA Type 1/IP21, 480V, FR7, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



Photo is representative

General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX040A1-4A1N1
UPC	Product Length/Depth
782116011544	10.1 in
Product Height	Product Width
24.8 in	9.3 in
Product Weight	Warranty
77.2 lb	2 year
Compliances	Certifications
Contact Manufacturer	UL 508C
	IEC 61800-2
	EN 61800-3 Level H

defaultTaxonomyAttributeLabel

[Brake chopper](#)

No brake chopper

[Modification](#)

Standard boards

[Horsepower](#)

40 hp

[Frame size](#)

7

[Keypad](#)

Alphanumeric

[Input](#)

EMC H

Three-phase

[Rating](#)

NEMA 1, IP21

[Software](#)

Standard

Resources

[Application notes](#)

[Electromagnetic compatibility \(EMC\)](#)

[Connecting drives to generator supplies](#)

[SPL - Variable frequency drives with a common DC bus](#)

[Brochures](#)

[SVX9000 Adjustable Frequency Drives Brochure](#)

[SVX9000 Adjustable Frequency Drives Product Aid](#)

[Catalogs](#)

[Product Range Catalog Drives Engineering](#)

[Eaton's Volume 6—Solid-State Motor Control](#)

[Product Datasheet - SVX040A1-4A1N1](#)

[Drawings](#)

[SVX_\(FR7\) 2D PDF](#)

[SVX_\(FR7\) AutoCAD 2D Footprint \(mm\)](#)

[SVX_\(FR7\) 3D Inventor](#)

[SVX_\(FR7\) 2D Drawing Xchange](#)

[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)

[SVX_\(FR7\) 3D Model Xchange](#)

[SVX_\(FR7\) AutoCAD 2D Footprint](#)

[Installation instructions](#)

[9000X AFD User Manual](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - SVX040A1-4A1N1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)