

Eaton XTCE018C10E

Catalog Number: XTCE018C10E

Eaton XT IEC contactor, 18A, 208 Vac, 60 Hz, 1NO, 18A, Frame C, 45 mm, 60 Hz, 2, 2, 3/ 5, 5, 10, 15 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Non-reversing, , Screw terminals, FVNR



Photo is representative

General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	XTCE018C10E
EAN	Product Length/Depth
4015082769987	3.425 in
Product Height	Product Width
3.898 in	1.85 in
Product Weight	Warranty
0.9 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
RoHS Compliant	IEC 60947
	UL Listed
	EN 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

18A

HP rating - max

2, 2, 3/ 5, 5, 10, 15 hp (1/3PH @ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

60 Hz

Frame size

45 mm

Terminals

Screw terminals

Coil

208 Vac, 60 Hz

Coil voltage

208 Vac, 60 Hz

Contact configuration

1 NO

Continuous ampere rating

18 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

[XTCE_C 2D Drawing Xchange](#)

[XTCE_C AutoCAD 2D Footprint](#)

[XTCE_C 3D Model Xchange](#)

[XTCE_C 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCE018C10E](#)

[Global Data Sheet - XTCE018C10E](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)