






circular conduc. terminal TA1.5 1 AWG...600 kcmil max. 400 A Cu cable 3 units
accessory for: 3VA53/54; 3VA63/64



Model		
product brand name	SENTRON	
accessories	Wire connector	
General technical data		
designation / of the terminal	TA1.5	
type of electrical connection / with control wire tap	No	
Connections according IEC		
connectable conductor cross-section		
<ul style="list-style-type: none"> for copper cable / stranded / minimum 	50 mm ²	
<ul style="list-style-type: none"> for copper cable / stranded / maximum 	300 mm ²	
<ul style="list-style-type: none"> for aluminum cable / stranded / minimum 	50 mm ²	
<ul style="list-style-type: none"> for aluminum cable / stranded / maximum 	300 mm ²	
stripped length	28 mm	
tightening torque / when using copper cables		
<ul style="list-style-type: none"> stranded 	50 - 300 mm ² : 42.4 Nm	
<ul style="list-style-type: none"> finely stranded 	50 - 240 mm ² : 42.4 Nm	
Connections according UL		
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C	
stripped length	1.1 in	
connectable conductor cross-section		
<ul style="list-style-type: none"> for copper cable / stranded / minimum 	1 AWG	
<ul style="list-style-type: none"> for copper cable / stranded / maximum 	600 kcmil	
<ul style="list-style-type: none"> for aluminum cable / stranded / minimum 	1 AWG	
<ul style="list-style-type: none"> for aluminum cable / stranded / maximum 	600 kcmil	
tightening torque / when using copper cables		
<ul style="list-style-type: none"> stranded 	1 AWG - 600 kcmil: 375 lb-in	
Certificates		
General Product Approval	EMV	
  	Miscellaneous  	
Marine / Shipping	other	Environment

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9373-0JB13>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9373-0JB13>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9373-0JB13

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

1/14/2024 

