

Vapor Barrier Ceiling Box, 4" Round, Non-Metallic

By TradeSelect
Catalog # [2028FBAR](#)



Vapor Barrier Ceiling Box, 4" Round, Non-Metallic, Flanged with Vapor Barrier

Features

- Self-clamping wire entry clamps
- Vapour/air barrier flange and integral wire entry seal provides superior energy savings and quick installation
- Hands free installation for 1/2", 5/8", or 3/4" drywall
- Front mounted grounding screw with combination straight/Robertson head

General

Bracket Setback	0.50
Cable Clamps	4
Material	Thermoplastic Resin
Style	Vapor Barrier
UPC	805035054536
Volume	28.1
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	2.625 in
Depth	2.625 in
Fixture Lbs.	50 lb
Height	3.150 in
Weight	.265 lb
Width	5.118 in

Certifications and Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	40
Pallet Quantity	1600

Product Assets

[3D Product View](#)
[Brochures - H3672 Banana Boxes](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)

