

ASP70-CCT-WH

LOW PROFILE LED FLUSH MOUNT



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS

WIRING:	Installs easily in traditional junction boxes (3" or 4") using the mounting bracket.
HOUSING DETAILS:	The ASPEN housings have a corrosion-resistant plastic construction. Sleek modern design, 0.7" (18mm) thickness. The unit is completely protected from moisture infiltration, giving it its WET location rating.
OPTICS:	LED technology delivers 1000 lumens (7" version) and 2000 lumens (12" version).
ELECTRICAL:	Energy efficient LED utilizing a 120V 60Hz driver. Certifications: ETL listed to U.S. and Canadian safety standards, per the UL1598 standards. Listed Title 24 per the California Energy Commission (CEC) standards. Meets NFPA 70, Nec section 410.16, C(1) requirements for use in closet storage spaces
LENS:	LED technology in combination with a white acrylic frosted lens, provides an even light distribution.

COLOR TEMPERATURE:	27K • 3K • 35K • 4K • 5K selectable
OPERATING TEMPERATURE:	-13°F (-25°C) + 104°F (40°C)
CRI:	90+
LUMEN OUTPUT:	1000 lumens
DIMMABLE:	Yes
WATTS:	14 Watts
LED LIFE:	50,000 hours
WARRANTY:	5 years
VOLTAGE:	120V
DIAMETER:	7.1" (180 mm)
HEIGHT:	0.7" (18 mm)
INTEGRATED MOTION SENSOR:	No



APPLICATIONS

The Aspen Series LED flush mounts provide general illumination with a sleek modern design suitable for indoor or outdoor residential and commercial applications. Ideal for use in closets, foyers, hallways, bedrooms, offices, utility work areas, stairways, and many other rooms in the house or work place environment.

ASP70-CCT-WH

LOW PROFILE LED FLUSH MOUNT

DIMENSIONS



RATINGS



ORDERING GUIDE

ASPEN SERIES

Series	Color Temperature	Finish
ASP70	CCT 27K-3K-35K-4K-5K/90CRI/14W	WH White
ASP70	CCT 27K-3K-35K-4K-5K/90CRI/14W	BK Black
Notes:	Configure product using BOLD options: Ex: ASP70-CCT-WH	