## SATCO NUVO

Project Name

Location Prepared By



Notes			

www] 01-15-2024 02:40:1

Status	Active
Watts	8.8W
Incandescent Equivalent	60W
Volts	120V-277V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	90+
Lumens	800L
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	25000
Lamp Type	Туре А
Technology	LED
Electrical	
Operating Frequency	60Hz
Power Factor	0.95/0.82
a <del>-</del>	250 ( 125) : 150 ( 1125)

Liectrical		
Operating Frequency	60Hz	
Power Factor	0.95/0.82	
Operating Temperature	-25C (-13F) to +45C (+113F)	
Physical		
MOL	4.00	

4.33
2.36
White
0.11

Additional Information			
Rated For Enclosed Fixture	Yes		
Warranty	5 Year Limited - 10 hr per day		

Compliance		
Safety Listing	cULus - Listed	
Location Rating	Damp	
Energy Star	No	
CA T20 / T24 Rationale	T20 Listed	
California Status	Lawful for sale in California	
Title 20 / 24 Status	Lawful for sale	
RoHS Compliant	Yes	
SDS Sheet	LED Lamp	

