

Eaton SVX010A1-4A1B1

Catalog Number: SVX010A1-4A1B1

Eaton SVX adjustable frequency drive, 10HP, NEMA Type 1/IP21, 480V, FR5, Three-phase, EMC H, Standard Software, A/N keypad, Internal brake chopper, Standard boards



Photo is representative

General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX010A1-4A1B1
UPC	Product Length/Depth
782116011490	8.4 in
Product Height	Product Width
16.5 in	5.6 in
Product Weight	Warranty
17.9 lb	2 year
Compliances	Certifications
Contact Manufacturer	IEC 61800-2
	UL 508C
	EN 61800-3 Level H

[Brake chopper](#)

Brake chopper

[Modification](#)

Standard boards

[Horsepower](#)

10 hp

[Frame size](#)

5

[Keypad](#)

Alphanumeric

[Input](#)

Three-phase

EMC H

[Rating](#)

NEMA 1, IP21

[Software](#)

Standard

[Application notes](#)

Electromagnetic compatibility (EMC)

Connecting drives to generator supplies

SPI - Variable frequency drives with a common DC bus

[Brochures](#)

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

[Catalogs](#)

Product Datasheet - SVX010A1-4A1B1

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

[Drawings](#)

SVX and SPX Series FR4-FR11 PDF Open Drawings

SVX_(FR5) AutoCAD 2D Footprint

SVX_(FR5) 2D PDF

SVX_(FR5) 2D Drawing Xchange

SVX_(FR5) AutoCAD 2D Footprint (mm)

SVX_(FR5) 3D Inventor

SVX_(FR5) 3D Model Xchange

[Installation instructions](#)

9000X AFD User Manual

[Specifications and datasheets](#)

Eaton Specification Sheet - SVX010A1-4A1B1