

# Eaton SVX015A1-4A1B1

Catalog Number: SVX015A1-4A1B1

Eaton SVX adjustable frequency drive, 15HP, NEMA Type 1/IP21, 480V, FR5, Three-phase, EMC H, Standard Software, A/N keypad, Internal brake chopper, Standard boards



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton SVX adjustable frequency drive	SVX015A1-4A1B1
<b>UPC</b>	<b>Product Length/Depth</b>
782116011506	8.4 in
<b>Product Height</b>	<b>Product Width</b>
16.5 in	5.6 in
<b>Product Weight</b>	<b>Warranty</b>
17.9 lb	2 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	EN 61800-3 Level H
	UL 508C
	IEC 61800-2

[Brake chopper](#)

Brake chopper

[Modification](#)

Standard boards

[Horsepower](#)

15 hp

[Frame size](#)

5

[Keypad](#)

Alphanumeric

[Input](#)

Three-phase

EMC H

[Rating](#)

NEMA 1, IP21

[Software](#)

Standard

[Application notes](#)

SPI - Variable frequency drives with a common DC bus

Electromagnetic compatibility (EMC)

Connecting drives to generator supplies

[Brochures](#)

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

[Catalogs](#)

Eaton's Volume 6—Solid-State Motor Control

Product Range Catalog Drives Engineering

Product Datasheet - SVX015A1-4A1B1

[Drawings](#)

SVX and SPX Series FR4-FR11 PDF Open Drawings

SVX\_(FR5) AutoCAD 2D Footprint

SVX\_(FR5) AutoCAD 2D Footprint (mm)

SVX\_(FR5) 2D Drawing Xchange

SVX\_(FR5) 2D PDF

SVX\_(FR5) 3D Model Xchange

SVX\_(FR5) 3D Inventor

[Installation instructions](#)

9000X AFD User Manual

[Specifications and datasheets](#)

Eaton Specification Sheet - SVX015A1-4A1B1