

Eaton SVX015A1-5A4B1

Catalog Number: SVX015A1-5A4B1

Eaton SVX adjustable frequency drive, 15 Hp, AFD Software Series, NEMA 1, IP21, 690V , Alphanumeric keypad, Internal brake chopper circuit, Standard boards, 0 to Vin, FR6, Three-phase



Photo is representative

General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX015A1-5A4B1
UPC	Product Length/Depth
782116929207	10.1 in
Product Height	Product Width
24.8 in	9.3 in
Product Weight	Warranty
77.2 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked	EN 61800-5-1
Fulfills all EMC immunity requirements	UL Listed
	cUL Listed

Brake chopper

Internal brake chopper

Modification

Standard boards

Horsepower

15 hp

Phase

Three-phase

Frame size

6

Keypad

Alphanumeric

Output voltage

0 to Vin

Enclosure

NEMA 1, IP21

Humidity

0-95%

Software

AFD software series

Overload current

Overload 150% IH, 110% IL for 1 min

Application notes[SPI - Variable frequency drives with a common DC bus](#)[Connecting drives to generator supplies](#)[Electromagnetic compatibility \(EMC\)](#)**Brochures**[SVX9000 Adjustable Frequency Drives Brochure](#)[SVX9000 Adjustable Frequency Drives Product Aid](#)**Catalogs**[Product Datasheet - SVX015A1-5A4B1](#)[Eaton's Volume 6—Solid-State Motor Control](#)[Product Range Catalog Drives Engineering](#)**Drawings**[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)**Installation instructions**[9000X AFD User Manual](#)**Specifications and datasheets**[Eaton Specification Sheet - SVX015A1-5A4B1](#)