



T8 High CRI Lamps

F32T8/TL941/ALTO 30PK

Philips T8 High CRI lamps featuring ALTO II technology are ideal when better color rendering properties are preferred.

Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Features | ALTO® (ALTO) |
| Light Technical | |
| Color Code | 940 [CCT of 4000K] |
| Beam Angle (Nom) | 0 degree(s) |
| Luminous Flux | 2,600 lm |
| Color Designation | 4100 Kelvin |
| Correlated Color Temperature (Nom) | 4100 K |
| Color rendering index (CRI) | >90 |
| Operating and Electrical | |
| Power Consumption | 32 W |
| Lamp Current (Nom) | 265 mA |
| Wattage Equivalent | 32 W |
| Voltage (Nom) | 137 V |
| Voltage (Nom) | 137 V |

| Mechanical and Housing | |
|---------------------------------|-----------------------|
| Bulb Finish | Coated glass |
| Bulb Shape | T-8 (T8) |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 1.7 mg |
| Product Data | |
| Order product name | F32T8/TL941/ALTO 30PK |
| Full product name | F32T8/TL941/ALTO 30PK |
| Order code | 479626 |
| Material Nr. (12NC) | 927871203901 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677479626 |
| Numerator - Packs per outer box | 30 |
| EAN/UPC - Case | 50046677479621 |

T8 High CRI Lamps

Dimensional drawing

| Product | C (max) | D (max) |
|-----------------------|------------|---------|
| F32T8/TL941/ALTO 30PK | 1,213.6 mm | 27.9 mm |

