



CorePro Plastic (Dimmable) A-Shape Lamps

8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	250 degree(s)
Luminous Flux	800 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz

Input Frequency	60 Hz
Power Consumption	8.8 W
Lamp Current (Nom)	80 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	90 ℃
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19


Datasheet, 2024, February 16 data subject to change

CorePro Plastic (Dimmable) A-Shape Lamps

UL Wet/ damp/ dry location	Damp location	
Approval and Application		
Energy Consumption kWh/1000 h	- kWh	
Energy Certifications	Energy Star	
T20 compliant	Yes	
Application Conditions		
can it be used in closed luminaires	Yes	
Product Data		
Order product name	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	


Full product name	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	
Order code	550442	
Material Nr. (12NC)	929002036204	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	046677550448	
Numerator - Packs per outer box	6	
EAN/UPC - Case	50046677550443	

Dimensional drawing




Product	D	С
8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm

Photometric data








General uniform lighting - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT


CorePro Plastic (Dimmable) A-Shape Lamps


Photometric data



Spectral Power Distribution Colour - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

Lifetime





Life Expectancy Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

Lumen Maintenance Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.