

LSLMS24-CCT-WH

Low Profile Strip Light



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS


WIRING:	Hardwire only. Installs easily to ceiling or wall. It may also be installed over a junction box using a canopy plate for an octagonal junction box. Manufactured as a two-part unit; easily removed front panel and a wire back housing to allow for ease of installation.
HOUSING DETAILS:	The housing channel is formed steel with durable poly carbonate end caps, with multiple 1/2" knockout locations for ease of installation. The motion sensor is a PIR sensor with a detection range of 13'(4m) to 19'(6m) and a time delay of 3 minutes. Sensing no movement within that time period, the unit will shut off automatically. Also included inside the wiring cavity is an ON/OFF Override Switch, if needed.
OPTICS:	Offered with an acrylic frosted diffuser lens and LED strip technology to distribute light and optimize delivered high level of lumens.
ELECTRICAL:	Easily connected to a 120-277V power supply via provided UL recognized driver. Non-dimmable DAMP LOCATIONS rated Certifications: This product is ETL and Energy Star listed in USA and Canada.
LENS:	Viper Light Strip has a frosted diffuser providing a uniform and widespread illumination.

COLOR TEMPERATURE:	3K - 35K -4K selectable
CRI:	80+
LUMEN OUTPUT:	1600
DIMMABLE:	No
WATTS:	16 W
LED LIFE:	50,000 hours
WARRANTY:	5 years
VOLTAGE:	120-277V
HEIGHT:	1.80" (4.6cm)
LENGTH:	22.80" (57.9cm)
WIDTH:	1.60" (4.1cm)
INTEGRATED MOTION SENSOR:	Yes
MOTION SENSOR DETECTION RANGE:	13' - 19' (4m - 9m)

APPLICATIONS

Low-profile LED strip light equipped with a PIR motion sensor. Ideal for many applications including corridors, laundry rooms, workshops, utility work areas, closet spaces and stairways.

DIMENSIONS



ACCESSORIES



5" JUNCTION BOX COVER PLATE

This j-box cover has been designed to work with the viper series of products. It will protect an existing electrical j-box to prevent unsightly installation and potential damage. Once installed, the j-box cover plate offers a clean and neat appearance for the light unit. Fits to cover standard octagon junction box. Painted white finish with 2 painted white screws included. 1/2" centre knockout hole for easy wiring and installation.

RATINGS



ORDERING GUIDE

VIPER CCT STRIP LIGHT SERIES

Series	Length	Color Temperature	Finish
LSLMS	24	CCT 3000K-3500K-4000K	WH White
Notes: Configure product using BOLD options: Ex: LSLMS24-CCT-WH			