

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NO.	DESCRIPTION	WEIGHT
NK5E88M**Y	8 POSITION, 8 WIRE CATEGORY 5E UNIVERSAL (A/B) MODULAR JACK. TERMINATION CAP IS COLOR CODED FOR T568 WIRING SCHEMES.	.66 lb/50 PCS [300 g/50 PCS]

NOTES:

- SEE WWW.PANDUIT.COM FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- MATERIAL:
MODULE HOUSING: POLYCARBONATE
NOMINAL WALL THICKNESS: .078(2.0)
TERMINATION CAP: POLYCARBONATE.
- ALL 8 POSITION, 8 WIRE CONNECTOR MODULES WILL ACCEPT THREE OR FOUR PAIR MODULAR PLUGS WITHOUT DAMAGE.
- DIMENSIONS IN [] ARE METRIC.



PANEL OPENING REQUIREMENTS
PANEL THICKNESS: (.048" - .058")



ACTUAL SIZE

PART NUMBER		NK5E88M**Y	
TITLE		NETKEY TWISTED PAIR CONNECTOR MODULE	
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479NK/02	
DATASET FILE NAME		M02479NK_DC350/02A	
THIRD ANGLE PROJECTION			
MATERIAL		SEE NOTE 2	
DRAWING NUMBER		02479-350	
REV	DATE	BY	CHK
02A	2-1-2024	BJN	ROJC
MMR			
DESCRIPTION		ECN	SCALE
UPDATED TITLE BLOCK MODULE HOUSING MATERIAL WAS ABS REVISED & REDRAWN PREVIOUS REVIS REMVD FOR CLARITY		M09000VN	FULL
SHEET 1 OF 1		SIZE	
A		A	

2

1

A-SIZE CUSTOMER