

Eaton XTCE080F00A

Catalog Number: XTCE080F00A

Eaton XT IEC contactor, 80A, 110 Vac 50 Hz, 120 Vac 60 Hz, ONO-ONC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15, 15/ 25, 30, 60, 75 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR



Photo is representative

General specifications

Product Name

Eaton XT IEC contactor

EAN

4015082393991

Product Height

7.25 in

Product Weight

6.23 lb

Certifications

UL Listed

CSA Certified

IEC 60947

EN 60947

Catalog Number

XTCE080F00A

Product Length/Depth

7 in

Product Width

4 in

Compliances

RoHS Compliant

CE Marked

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

80A

HP rating - max

7.5, 15, 15/ 25, 30, 60, 75 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

90 mm

Terminals

Screw terminals

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

0 NO, 0 NC

Continuous ampere rating

80 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_F 3D Model Xchange](#)

[XTCE_F 2D Drawing Xchange](#)

[XTCE_F 3D Inventor](#)

[XTCE_F AutoCAD 2D Footprint](#)

[XTCE_F 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCE080F00A](#)

[Global Data Sheet - XTCE080F00A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)