



RRD151WTR

By Hubbell Wiring Device-Kellems
Catalog # [RRD151WTR](#)

TradeSELECT® Straight Blade Residential Grade, Tamper Resistant Decorator Single, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R.



Application

Residential Receptacles

General

Color	<ul style="list-style-type: none">• White• Blanc
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	883778302077

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK Z-5 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - RRD151WTR AutoCAD Drawing](#)
[Literature - Tamper-Resistant Receptacles for Residential Applications](#)
[Literature - Tamper-Resistant Receptacles for Daycare](#)
[Literature - Tamper-Resistant Receptacles](#)
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)
[Literature - Residential Product Guide](#)
[Literature - Residential Catalog](#)
[Sales Drawings - WDK_RRD151TR_DRAWING_PDF](#)
[Video - Tradeselect Devices](#)
[Video - Tamper-Resistant Receptacles](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-RRD151WTR-SPEC-EN | REV 1/2024