

# Eaton XTCE009B10D

Catalog Number: XTCE009B10D

Eaton XT IEC contactor, 9A, 600 Vac, 60 Hz, 1NO, 9A, Frame B, 45 mm, 60 Hz, 0.5, 1, 1.25/ 3, 3, 5, 7.5 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Non-reversing, , Screw terminals, FVNR



Photo is representative

## General specifications

### Product Name

Eaton XT IEC contactor

### EAN

4015081548170

### Product Height

2 in

### Product Weight

0.5 lb

### Certifications

UL Listed

CSA Certified

IEC 60947

EN 60947

### Catalog Number

XTCE009B10D

### Product Length/Depth

3 in

### Product Width

3 in

### Compliances

CE Marked

RoHS Compliant

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## defaultTaxonomyAttributeLabel

### Amperage Rating

9A

### HP rating - max

0.5, 1, 1.25/ 3, 3, 5, 7.5 hp (1/3PH  
@115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

60 Hz

### Terminals

Screw terminals

### Coil voltage

600 Vac, 60 Hz

### Contact configuration

1 NO

### Continuous ampere rating

9 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_B 3D Inventor](#)

[XTCE\\_B 2D PDF](#)

[XTCE\\_B AutoCAD 2D Footprint](#)

[XTCE\\_B 3D Model Xchange](#)

[XTCE\\_B 2D Drawing Xchange](#)

### Specifications and datasheets

[Global Data Sheet - XTCE009B10D](#)

[Eaton Specification Sheet - XTCE009B10D](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)