



T8 High CRI Lamps

F32T8/TL965/ALTO 30PK

Philips T8 High CRI lamps featuring ALTO II technology are ideal when better color rendering properties are preferred.

Product data

General Information		
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	
Features	ALTO® (ALTO)	
Light Technical		
Color Code	965 [CCT of 6500K]	
Beam Angle (Nom)	0 degree(s)	
Luminous Flux	2,600 lm	
Color Designation	6500 Kelvin	
Correlated Color Temperature (Nom)	6500 K	
Color rendering index (CRI)	>90	
Operating and Electrical		
Power Consumption	32 W	
Lamp Current (Nom)	265 mA	
Wattage Equivalent	32 W	
Voltage (Nom)	137 V	
Voltage (Nom)	137 V	

Mechanical and Housing		
Bulb Finish	Coated glass	
Bulb Shape	T-8 (T8)	
Approval and Application		
Mercury (Hg) Content (Nom)	1.7 mg	
Product Data		
Order product name	F32T8/TL965/ALTO 30PK	
Full product name	F32T8/TL965/ALTO 30PK	
Order code	927871205701	
Material Nr. (12NC)	927871205701	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	046677479640	
Numerator - Packs per outer box	30	
EAN/UPC - Case	50046677479645	

Datasheet, 2023, November 6 data subject to change

T8 High CRI Lamps

Dimensional drawing

Product	C (max)	D (max)
F32T8/TL965/ALTO 30PK	1,213.6 mm	27.9 mm



