

# Eaton CPM120

Catalog Number: CPM120

Eaton BR main breaker loadcenter, CPM Plug-in Loadcentre, Combination, Main Circuit Breaker, 100A, BR, Breaker: 100A, Flush/Surface, #4-1/0 AWG, Three-wire, 120/240V, Single Phase, NEMA 1, 16 gauge galvanized sheet steel, 20/40 circuits



## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	CPM120
UPC	Product Length/Depth
622588060193	14.38 in
Product Height	Product Width
27 in	3.88 in
Product Weight	Certifications
18 lb	Contact Manufacturer

## Catalog Notes

Replaced By CPM120WL

## Product specifications

### Type

Combination

### Cover

Flush/surface

### Phase

Single-phase

### Enclosure

NEMA 1

### Number of circuits

16

### Voltage rating

120/240 V

### Amperage Rating

100 A

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CPM120](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)