

Eaton CN15KN3A

Catalog Number: CN15KN3A

Eaton Freedom NEMA Contactor, Full voltage non-reversing, NEMA Size 3 open enclosure - 90 A, Three-pole, 120/60 or 110/50 coil voltage



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control contactor	CN15KN3A
	UPC
	782113603919
Product Length/Depth	Product Height
5.94 in	7.17 in
Product Width	Product Weight
4.08 in	8 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Certified
	Catalog Notes
	Common Control

defaultTaxonomyAttributeLabel

NEMA frame size

NEMA Size 3

Relay

None

Type

Contactors

Configuration

Non-reversing

Phase

Three-phase

Amperage Rating

90 A

Size

3

Horsepower

25 hp at 208 V, 30 hp at 240 V, 50 hp at 480/600 V

Overload relay

None

Coil voltage

120/60 or 110/50

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[CN15KN3 3D Inventor](#)

[CN15KN3 2D Drawing Xchange](#)

[CN15KN3 2D PDF](#)

[CN15KN3 3D Model Xchange](#)

[CN15KN3 AutoCAD 2D Footprint \(mm\)](#)

[CN15KN3 AutoCAD 2D Footprint](#)

Specifications and datasheets

[Quick Selector - NEMA Contactors](#)

[Eaton Specification Sheet - CN15KN3A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)