

Eaton DA1-35022NB-A20C

Catalog Number: DA1-35022NB-A20C

Eaton DA1 Series Enclosure Drive Three-phase mains connection/three-phase motor connection 600V Internal brake chopper LED display IP20 22A 15 kW FR3 20 Hp AF drive 50/60 Hz



General specifications

Product Name	Catalog Number
Eaton PowerXL DA1 adjustable frequency drive	DA1-35022NB-A20C
	UPC
	786685891217
Product Length/Depth	Product Height
8.03 in	10.75 in
Product Width	Product Weight
5.16 in	7.55 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the CE Marked date of shipment of the Product, whichever occurs first.	C-Tick Compliant
	Certifications
	cUL Listed
	EN 61800-3
	EN 61800-5-1
	UL Listed
	EN 60529
	UkrSepro

defaultTaxonomyAttributeLabel

Brake chopper

Internal brake chopper

Amperage Rating

22A

Horsepower

20 hp

Phase

Three-phase main, three-phase motor

Serial interface

RS-485 CANopen

Special features

Coated printed circuit boards

Type

AF drive

Voltage rating

600 V

Frequency rating

50-60 Hz

Frame size

3

Display

LED

NEMA rating

IP20

Power consumption

15 kW

Resources

Catalogs

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - DA1-35022NB-A20C

Drawings

DA1_A20C(FR3) 3D Model Xchange

DA1_A20C(FR3) 3D Inventor

DA1_A20C(FR3) AutoCAD 2D Footprint (mm)

DA1_A20C(FR3) 2D PDF

DA1_A20C(FR3) 2D Drawing Xchange

DA1_A20C(FR3) AutoCAD 2D Footprint

Specifications and datasheets

Eaton Specification Sheet - DA1-35022NB-A20C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)