

Eaton 5369

Catalog Number: 5369

Eaton Arrow Hart ultra grip straight blade connector, #16-12 AWG, 20A, Industrial, 125V, Back wire, Black and white, Brass, Nylon, 5-20R, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Nylon, Core pack

General specifications



| | |
|--|----------------|
| Product Name | Catalog Number |
| Eaton Arrow Hart ultra grip straight blade connector | 5369 |
| | UPC |
| | 032664390609 |

| | |
|----------------------|----------------|
| Product Length/Depth | Product Height |
| 6.5 in | 1.5 in |

| | |
|---------------|----------------|
| Product Width | Product Weight |
| 3.5 in | 0.176 lb |

Certifications

UL
NOM
Federal Specification Classification 6221
02
cULus Listed

Electrical Ratings

Amperage Rating

20A

NEMA configuration

5-20R

Voltage rating

125V

Wiring method

Back wire

Material Specifications

Color

White

Black

Contact material

Brass

Face/body material

Nylon

Material

Nylon

Packaging type

Core pack

Product Specifications

Allowable wire size

#16-12 AWG

Application

Industrial

Connection type

Screw

Cord range

0.33-0.66" in diameter

Design type

Straight blade

Device grade

Extra heavy-duty industrial specification grade

Device type

Connector

Number Of Poles

Two-pole

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Style type

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 5369](#)

Straight body

Type

Connector



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia