

Eaton 5466

Catalog Number: 5466

Eaton Arrow Hart ultra grip straight blade plug, #18-12 AWG, 20A, Industrial, 250V, Back wire, Black and white, Brass, Nylon, 6-20P, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Polycarbonate, Core pack

General specifications



Product Name	Catalog Number
Eaton Arrow Hart ultra grip straight blade plug	5466
	UPC
	032664393907

Product Length/Depth	Product Height
1.51 in	7 in

Product Width	Product Weight
1.51 in	0.1 lb

Certifications

UL

NOM

Federal Specification Classification 6221

02

Electrical Ratings

Amperage Rating

20A

NEMA configuration

6-20P

Voltage rating

250V

Wiring method

Back wire

Material Specifications

Color

White

Black

Contact material

Brass

Face/body material

Nylon

Material

Polycarbonate

Packaging type

Core pack

Product Specifications

Allowable wire size

#18-12 AWG

Application

Industrial

Connection type

Screw

Cord range

0.33-0.66" in diameter

Design type

Straight blade

Device grade

Extra heavy-duty industrial specification grade

Device type

Plug

Number Of Poles

Two-pole

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Style type

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 5466](#)

Straight body

Type

Plug



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)