

# Eaton 5669

Catalog Number: 5669

Eaton Arrow Hart severe duty straight blade connector, #18-12 AWG, 15A, Industrial, 250V, Back wire, Black and white, Nickel-plated brass, Corrosion Resistant, Nylon, 6-15R, Two pole, three wire, grounding, Screw, 0.38-1" in diameter, Nylon, Core pack



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart severe duty straight blade connector	5669
	<b>UPC</b>
	032664392504
<b>Product Length/Depth</b>	<b>Product Height</b>
6.5 in	1.5 in
<b>Product Width</b>	<b>Product Weight</b>
3.5 in	0.165 lb

## Certifications

UL  
NOM  
Federal Specification Classification 6221  
02

## defaultTaxonomyAttributeLabel

### Device type

Connector

### Type

Complex environment

### Amperage Rating

15A

### Voltage rating

250V

### Contact material

Nickel-plated brass

### Application

Industrial

### Device grade

Severe duty

### Wiring method

Back wire

### Environmental conditions

Corrosive

### Number of wires

3

### Number Of Poles

Two-pole

### Style type

Straight body

### Cord range

0.38-1" in diameter

### Material

Nylon

### Packaging type

Core pack

### Environmental resistance

Corrosion resistant

### Color

Black

White

## Resources

### Brochures

[Wiring Devices Buyer's Guide](#)

### Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

### Specifications and datasheets

[Eaton Specification Sheet - 5669](#)

Connection type

Screw

Allowable wire size

#18-12 AWG

NEMA configuration

6-15R

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)