

Eaton IG5262RN

Catalog Number: IG5262RN

Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle,#14-10 AWG,15A,Industrial,Flush,125V,Back and side,Orange,Brass,High-impact nylon face,Glass-filled nylon base,5-15R,Duplex,Screw,Glass-filled nylon,.



General specifications

| | |
|--|--|
| Product Name | Catalog Number |
| Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle | IG5262RN |
| | UPC |
| | 032664735387 |
| Product Length/Depth | Product Height |
| 1.3 in | 4.19 in |
| Product Width | Product Weight |
| 0.89 in | 0.37 lb |
| Compliances | Certifications |
| RoHS Compliant | UL |
| | NOM |
| | Federal Specification Classification 6233 01 |

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Isolated ground

Auto-grounding

Terminal guards

Screw-catch

Application

Industrial

Device grade

Heavy-duty industrial specification grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Glass-filled nylon

Color

Orange

Connection type

Screw

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Arrow Hart extra heavy duty industrial grade isolated ground straight blade receptacles](#)

[Eaton Specification Sheet - IG5262RN](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

High-impact nylon face

Glass-filled nylon base

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)