

Eaton IG5262W

Catalog Number: IG5262W

Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle, #14-10 AWG, 15A, Industrial, Flush, 125V, Back and side, White, Brass, High-impact nylon face, Glass-filled nylon base, 5-15R, Duplex, Screw, Glass-filled nylon, .



General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	IG5262W
	UPC
	032664735400
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.89 in	0.001 lb
Compliances	Certifications
RoHS Compliant	UL
	NOM
	Federal Specification Classification 6233 01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Isolated ground

Auto-grounding

Terminal guards

Screw-catch

Application

Industrial

Device grade

Heavy-duty industrial specification grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Glass-filled nylon

Color

White

Connection type

Screw

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - IG5262W](#)

[Arrow Hart extra heavy duty industrial grade isolated ground straight blade receptacles](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Glass-filled nylon base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)