

JA Series



200 AMP SOCKET & BREAKER Combination with or without breaker

CATALOGUE #	TYPE	DESCRIPTION	DIMENSIONS (IN.)			WEIGHT
			H	W	D	
JA402P	O/H	4 Jaw c/w 200 Amp breaker	25 ¹ / ₈	10 ¹ / ₈	5 ¹ / ₄	25 lbs.
JA402P-LB	O/H	as above, less breaker	25 ¹ / ₈	10 ¹ / ₈	5 ¹ / ₄	24 lbs.
JA402R	O/H & U/G	4 Jaw c/w 200 Amp breaker	29	12	5 ¹ / ₄	25 lbs.
JA402R-LB	O/H & U/G	as above, less breaker	29	12	5 ¹ / ₄	24 lbs.

- 200 Amp - 120/240 VOLT
- Combination meter socket & circuit breaker
- CSA enclosure 3R
- Conductor range #6 - 250 MCM CU/AL
- Suitable for temporary service, farm service, trailers, recreational parks, commercial and residential locations.
- Service entrance rated

- Also available with 125 Amp breaker or 150 Amp breaker upon request
- Also available less breaker
- Add suffix "-HI" for 22kA interrupting Rating Breaker

KNOCKOUT CODE	CONDUIT SIZE
G	1 ¹ / ₄ ", 1 ¹ / ₂ ", 2", 2 ¹ / ₂ "

