

S800S-UCB Characteristic B*

$I_{CU} = 50 \text{ kA}$; with interchangeable cage terminal



2CC0413225F0001



2CC0413224F0001



2CC0413225F0001



2CC0413225F0001



I_{CU} [kA]	Rated current [A]	Order details Type Code	Order code	GTIN EAN 76122712	Weight [kg]	Pack. unit
50	10	S801S-UCB10	2CCS861001R1105	02842	0.24	1
50	13	S801S-UCB13	2CCS861001R1135	02859	0.24	1
50	16	S801S-UCB16	2CCS861001R1165	02866	0.24	1
50	20	S801S-UCB20	2CCS861001R1205	02873	0.24	1
50	25	S801S-UCB25	2CCS861001R1255	02880	0.24	1
50	32	S801S-UCB32	2CCS861001R1325	02897	0.24	1
50	40	S801S-UCB40	2CCS861001R1405	02903	0.24	1
50	50	S801S-UCB50	2CCS861001R1505	02910	0.24	1
50	63	S801S-UCB63	2CCS861001R1635	02927	0.24	1
50	80	S801S-UCB80	2CCS861001R1805	02934	0.24	1
50	100	S801S-UCB100	2CCS861001R1825	02941	0.24	1
50	125	S801S-UCB125	2CCS861001R1845	02958	0.24	1
50	10	S802S-UCB10	2CCS862001R1105	02965	0.49	1
50	13	S802S-UCB13	2CCS862001R1135	02972	0.49	1
50	16	S802S-UCB16	2CCS862001R1165	02989	0.49	1
50	20	S802S-UCB20	2CCS862001R1205	02996	0.49	1
50	25	S802S-UCB25	2CCS862001R1255	03009	0.49	1
50	32	S802S-UCB32	2CCS862001R1325	03016	0.49	1
50	40	S802S-UCB40	2CCS862001R1405	03023	0.49	1
50	50	S802S-UCB50	2CCS862001R1505	03030	0.49	1
50	63	S802S-UCB63	2CCS862001R1635	03047	0.49	1
50	80	S802S-UCB80	2CCS862001R1805	03054	0.49	1
50	100	S802S-UCB100	2CCS862001R1825	03061	0.49	1
50	125	S802S-UCB125	2CCS862001R1845	03078	0.49	1
50	10	S803S-UCB10	2CCS863001R1105	03085	0.74	1
50	13	S803S-UCB13	2CCS863001R1135	03092	0.74	1
50	16	S803S-UCB16	2CCS863001R1165	03108	0.74	1
50	20	S803S-UCB20	2CCS863001R1205	03115	0.74	1
50	25	S803S-UCB25	2CCS863001R1255	03122	0.74	1
50	32	S803S-UCB32	2CCS863001R1325	03139	0.74	1
50	40	S803S-UCB40	2CCS863001R1405	03146	0.74	1
50	50	S803S-UCB50	2CCS863001R1505	03153	0.74	1
50	63	S803S-UCB63	2CCS863001R1635	03160	0.74	1
50	80	S803S-UCB80	2CCS863001R1805	03177	0.74	1
50	100	S803S-UCB100	2CCS863001R1825	03184	0.74	1
50	125	S803S-UCB125	2CCS863001R1845	03191	0.74	1
50	10	S804S-UCB10	2CCS864001R1105	03207	0.98	1
50	13	S804S-UCB13	2CCS864001R1135	03214	0.98	1
50	16	S804S-UCB16	2CCS864001R1165	03221	0.98	1
50	20	S804S-UCB20	2CCS864001R1205	03238	0.98	1
50	25	S804S-UCB25	2CCS864001R1255	03245	0.98	1
50	32	S804S-UCB32	2CCS864001R1325	03252	0.98	1
50	40	S804S-UCB40	2CCS864001R1405	03269	0.98	1
50	50	S804S-UCB50	2CCS864001R1505	03276	0.98	1
50	63	S804S-UCB63	2CCS864001R1635	03283	0.98	1
50	80	S804S-UCB80	2CCS864001R1805	03290	0.98	1
50	100	S804S-UCB100	2CCS864001R1825	03306	0.98	1
50	125	S804S-UCB125	2CCS864001R1845	03313	0.98	1

*For DC applications