

Loom & Tubing Accessories (Clamps, Clips)

***NEW** Vinyl Coated Steel Clamps

- Provides electrical insulation, vibration absorption, and protection of wire & cable, hydraulic hoses and loom/tubing from abrasion & shock
- Holds lines firmly in place
- Standard-Grade Stainless Steel for longer life
- **Insulation:** Clamps are dipped in PVC to provide excellent resistance to acids, moisture and salts. Temperature range: -40°C to +90°C (-40°F to 194°F)
- Contact Techspan if you require other sizes

D



Metal Width: 1/2" (12.7mm); Hole Diameter: 1/4"

ID Size	Actual Mounting Hole Diameter	Metal Thickness	10 PCS/PK	100 PCS/PK	500 PCS/PK
1/4" (6.4mm)	.268" (6.80mm)	0.8mm	766087	766087C	766087B
3/8" (9.5mm)	.268" (6.80mm)	0.8mm	766088	766088C	766088B
1/2" (12.7mm)	.268" (6.80mm)	0.8mm	766089	766089C	766089B
5/8" (15.9mm)	.268" (6.80mm)	0.8mm	766090	766090C	766090B
3/4" (19.1mm)	.268" (6.80mm)	0.8mm	766091	766091C	766091B
1" (25.4mm)	.268" (6.80mm)	0.8mm	766092	766092C	
1-1/4" (31.8mm)	.268" (6.80mm)	0.8mm	*766096	*766096C	
1-1/2" (38.1mm)	.268" (6.80mm)	0.8mm	766093	766093C	
2" (50.8mm)	.268" (6.80mm)	0.8mm	*766097	*766097C	

*NEW

*NEW

Metal Width: 5/8" (15.9mm); Hole Diameter: 3/8"

ID Size	Actual Mounting Hole Diameter	Metal Thickness	10 PCS/PK	100 PCS/PK	500 PCS/PK
1/4" (6.4mm)	.404" (10.25mm)	0.8mm	766058	766058C	766058B
3/8" (9.5mm)	.404" (10.25mm)	0.8mm	766074	766074C	766074B
1/2" (12.7mm)	.404" (10.25mm)	0.8mm	766059	766059C	766059B
5/8" (15.9mm)	.404" (10.25mm)	0.8mm	766075	*766075C	766075B
3/4" (19.1mm)	.404" (10.25mm)	0.8mm	766060	766060C	766060B

*NEW

Metal Width: 1" (25.4mm); Hole Diameter: 3/8"

ID Size	Actual Mounting Hole Diameter	Metal Thickness	10 PCS/PK	100 PCS/PK	500 PCS/PK
1" (25.4mm)	.404" (10.25mm)	1.1mm	766061	*766061C	766061B

*NEW

Vinyl Coated Steel Clamps



72-Hour Salt Spray Test

Why the change to Stainless Steel?

Material	Result
Zinc Electroplated Steel (previous version)	Subject to overall corrosion
Standard Grade Stainless Steel	Only minor corrosion on the edges
304-Grade Stainless Steel	No corrosion

