

Project Name

Location

Prepared By



**Notes**

[www] 12-26-2023 02:52:59

**General**

Status	Active
Watts	24W/32W/40W
Incandescent Equivalent	100W
Fluorescent Equivalent	40W/55W/70W
Volts	120V-277V
Shape	T8
Base	Single Pin
ANSI Base	Fa8
Nominal Length	96
Finish	White
CCT (Kelvin)	3000K/3500K/4000K/5000K/6500K
Temperature	Soft White to Daylight
CRI	82
Lumens	3500L/4400L/5500L
Beam Spread	210
Hours Rated	50000
Lamp Type	Linear
Technology	LED

**Electrical**

Ballasting Requirements	Type B Ballast Bypass
Operating Frequency	50/60Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to +45C (+113F)

**Physical**

MOL	93.75
MOD	1
Material	Glass
Weight (lb.)	0.98

**Additional Information**

Additional Info	DLC compatible only when using Fa8 Base
Includes	(20) R17d Base Adapters and (10) Fastening Clips included per case
Shatter-Proof Type	PET Coated
Installation Notes	Must use both sections
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

**Compliance**

Safety Listing	cULus - Classified; cRUus - Recognized Component
Location Rating	Damp
DLC Approved	Yes
DLC ID	S-HPN8SY
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes

FCC Compliant	Yes
NSF Approved	Yes

Copyright 2023 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<https://www.satco.com/>

