

Project Name

Location

Prepared By



## SATCO S28932R1

80W/LED/HID/SB/3CCT/EX39

### Notes

[www] 01-15-2024 02:40:10

### General

Status	Active
Watts	60W/70W/80W
Incandescent Equivalent	400W
HID Equivalent	200W/250W/320W
Volts	120V-277V
Shape	Integrated LED
Base	Mogul Extended
ANSI Base	EX39
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
CRI	80
Lumens	9000L/10150L/11200L
Beam Spread	180
Dimmable	Yes-Dimmable
Hours Rated	50000
Technology	LED
Min Compartment Size	Length: 11 in. Width: 11 in. Height: 9.2 in.

### Electrical

Operating Frequency	50/60Hz
Dimming Type	Step Dimming
Power Factor	>0.9
Operating Position	Universal
Surge Protection	Built-in surge protection - 4KV
THD	<20%
Operating Temperature	-30C (-22F) to +45C (+113F)

### Physical

MOL	8.86
MOD	8.9
Lens Material	Polycarbonate (PC)
Weight (lb.)	2.43

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

### Compliance

Safety Listing	cULus - Listed; cULus - Classified
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-ARHCWO
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
Colorado Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes



