

2967-20   2967-21B   2967-21F   **2967-22**



### M18 FUEL™ 1/2" High Torque Impact wrench w/ Friction Ring Kit

★★★★★ 4.9 (336) [Write a review](#)

Our M18 FUEL™ 1/2" High Torque Impact Wrench w/ Friction Ring Kit includes the most power dense impact wrench in its class, provides greater access in tight spaces, and maximizes productivity through faster removal speeds. The POWERSTATE™ Brushless Motor delivers up to 1,100 ft-lbs of Fastening Torque and 1,500 ft-lbs of Nut-Busting Torque when paired with our M18™ REDLITHIUM™ XC5.0 Battery, while the compact size at 7.6" in length gives users greater access in tight spaces. The M18 FUEL™ 1/2" High Torque Impact Wrench w/ Friction Ring maximizes productivity on the jobsite and in the shop by removing stubborn bolts and fasteners faster than cordless competitors. Our patented battery isolation system provides a secure battery connection and controls vibration transmitted to the pack. Tri-LEDs surround the anvil to deliver brighter light with fewer shadows. 4-Mode DRIVE CONTROL™ offers greater precision with a range of pre-set RPM and IPM levels, selectable from a single button on the tool. By selecting Mode 4, AUTO SHUT-OFF™ control applies no more than 50 ft-lbs of torque for hand-tight fastening applications to prevent overtightening. Mode 4 also features Bolt Removal Control that delivers our users full torque output, then decreases RPMs once the bolt is loosened to prevent fastener drops. The 1/2" Friction Ring design allows for quick & tool-free socket changes. The M18 REDLITHIUM™ XC5.0 Resistant Batteries included provide increased protection against oils, greases, & solvents.

[Close](#)

#### INCLUDES

- (1) M18 FUEL™ 1/2" High Torque Impact Wrench w/ Friction Ring (2967-20)
- (2) M18™ REDLITHIUM™ XC5.0 Resistant Battery (48-11-1850R)
- (1) M18™ & M12™ Multi-Voltage Charger (48-59-1812)
- (1) Hard Case

#### KEY FEATURES

- ✓ Most Power Dense - Best Combination of Power and Size.
- ✓ Up to 2" Shorter Length. 7.6" in length provides most access in tight spaces.
- ✓ Patented battery isolation system ensures a secure battery connection and controls vibration transmitted to the pack
- ✓ 4-Mode DRIVE CONTROL™ provides greater control over output speed and power. Includes auto shut-off and bolt-removal mode
- ✓ AUTO-SHUTOFF™ control prevents over tightening and increases productivity by applying no more than 50 ft-lbs of torque
- ✓ Mode 1 RPMs: 0 - 700; Mode 2 RPMs: 0 - 1,300; Mode 3 RPMs: 0 - 2,000; Mode 4 RPMs: FWD: 0 - 900, REV: 0 - 2,000 / 0 - 750
- ✓ M18™ REDLITHIUM™ XC5.0 Resistant Batteries included provides increased protection against oils, greases, and solvents
- ✓ Compatible with all M18™ batteries & chargers

#### SPECIFICATIONS

- ✓ POWERSTATE™ Brushless Motor delivers up to 1,100 ft-lbs of Fastening Torque & 1,500 ft-lbs of Nut-Busting Torque w/ M18™ REDLITHIUM™ XC5.0 Battery
- ✓ Fastest Removal Speeds. Maximize productivity on the jobsite and in the shop.
- ✓ Tri-LEDs deliver high definition lighting to increase workspace visibility with less shadows
- ✓ Bolt removal mode provides maximum nut-busting torque to break fastener free, then slows to 750 RPM for more control when removing fasteners
- ✓ Mode 1 IPMs: 0 - 1,300; Mode 2 IPMs: 0 - 2,200; Mode 3 IPMs: 0 - 2,400; Mode 4 IPMs: 0 - 2,400
- ✓ Friction ring (hog ring) ensures quick and easy socket changes
- ✓ REDLINK PLUS™ Intelligence: Ensures maximum performance and protects from overloads, heating, and over-discharge.

#### REVIEWS