



# Slim Flood LED (TF)

## Slim Flood, 10W, 4000K, Generation 1, Knuckle mount, 120-277VAC, Bronze finish

Slim Flood, 10W, 4000K, Generation 1, Knuckle mount, 120-277VAC, Bronze finish - 119 lm/W

Slim Flood LED Floodlights are your best value for discreet and modern design on your floodlighting projects. Versatile and stylish with six different sizes to choose from, Slim Flood provides application flexibility for ground, wall, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications. The discreet low profile design will not interfere with your landscape layouts.

### Product data

General information	
Lamp Source Code	LED
Colour Temperature	4000 K
CRI	80
Photometric Distribution Type	Flood
Mounting	NPT/NPS Ground / Floor Wall
Number Of Pieces	1
Grade	Value Grade
Operating and electrical	
Voltages	120/208/240/277 V
Luminaire Input Watts	9
Conduit Connection	7/8 inch knockout
Mechanical and housing	
Shape	Rectangular

Material	Aluminum
Enclosure	Metal and Plastic
Approval and application	
Safety Listing	ETL
Energy Certifications	DLC Standard cETLus
IP Rating	IP65 [ Dust penetration-protected, jet-proof]
Vibration Rating	1.5G
Initial performance (IEC compliant)	
Luminaire Lumens	1089
Efficacy	119 lm/W
Application conditions	
Ambient temperature range	-40 °C to 40 °C
Max Ambient Temp	40 °C

## Slim Flood LED (TF)

Min Ambient Temp	-40 °C
Min Ambient Temp-DUP(do not use)	-40 °C
<b>Product data</b>	
Full product code	911401733562
Order product name	TF10-NW-G1-K-FL-8-BZ
EAN/UPC - Product	783352025944
Order code	TF10-NW-G1-K-FL-8-BZ
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	18
Material Nr. (12NC)	911401733562
Net Weight (Piece)	0.550 kg
Catalog Number	TF10-NW-G1-K-FL-8-BZ
Catalog Number Description	Slim Flood, 10W, 4000K, Generation 1, Knuckle mount, 120-277VAC, Bronze finish

