



LED Post Top (PT)

PT50-NW-G1-T2-3-HV3-FAWS-TLRPC-BK

Post Top LED, Neutral White, Generation 1, tenon mount, Type 3, Field Adjustable Wattage Selector - 94 lm/W

The KEENE LED post top is compact and comfortable, with a sleek low profile design suitable for 10'-16' mounting heights. Features include low glare comfort optics, field adjustable output, twist lock receptacle with shorting cap, and an LED driver suitable for 120 volt through to 347 volt operation. The comfortable, low glare optics make this an ideal choice for pedestrian scale applications such as condominiums, hotel parking lots, parks and walkways.

Product data

General information	
Lamp Source Code	LED
Colour Temperature	4000 K
CRI	70
Photometric Distribution Type	Type III
Mounting	Pole Top
Number Of Pieces	1
Operating and electrical	
Voltages	120/277/347 V
Luminaire Input Watts	22 32 46 53 W
Mechanical and housing	
Enclosure	Metal and Plastic
Initial performance (IEC compliant)	
Luminaire Lumens	2500 4200 5300 6300 lm

Efficacy	94 lm/W
Product data	
Order product name	PT50-NW-G1-T2-3-HV3-FAWS-TLRPC-BK
EAN/UPC - Product	783352026088
Order code	912401482869
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401482869
Catalog Number	PT50-NW-G1-T2-3-HV3-FAWS-TLRPC-BK
Catalog Number Description	Post Top LED, Neutral White, Generation 1, tenon mount, Type 3, Field Adjustable Wattage Selector