



LED General Purpose Floods FL

FL300-NW-G1-S-FL-8-BZ

Floodlight, 300W, Slip Fitter Mount, 120-277V, Bronze Finish - 113 lm/W

The General Purpose LED Floodlights offer energy saving LED technology for long life and reduced maintenance. Versatile and stylish with five different sizes to choose from provides application flexibility for ground mount, wall mount, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications.

Product data

General information		Efficacy	
Lamp Source Code	LED		113 lm/W
Colour Temperature	4000 K	Product data	
CRI	70	Order product name	FL300-NW-G1-S-FL-8-BZ
Photometric Distribution Type	Flood	EAN/UPC - Product	783352025197
Mounting	Slip Fitter	Order code	912401475274
Number Of Pieces	1	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
Operating and electrical		Material Nr. (12NC)	912401475274
Voltages	120/208/240/277 V	Catalog Number	FL300-NW-G1-S-FL-8-BZ
Luminaire Input Watts	300 W	Catalog Number Description	Floodlight, 300W, Slip Fitter Mount, 120-277V, Bronze Finish
Mechanical and housing			
Enclosure	Metal and Plastic		
Initial performance (IEC compliant)			
Luminaire Lumens	34000 lm		

LED General Purpose Floods FL

