



Slim Flood LED (TF)

Slim Flood, 30W, 4000K, Generation 1, Knuckle mount, 120-277VAC, Bronze finish

Slim Flood, 30W, 4000K, Generation 1, Knuckle mount, 120-277VAC, Bronze finish - 115 lm/W

Slim Flood LED Floodlights are your best value for discreet and modern design on your floodlighting projects. Versatile and stylish with six different sizes to choose from, Slim Flood provides application flexibility for ground, wall, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications. The discreet low profile design will not interfere with your landscape layouts.

Product data

General information		Material	Aluminum
Lamp Source Code	LED	Enclosure	Metal and Plastic
Colour Temperature	4000 K	Approval and application	
CRI	80	Safety Listing	ETL
Photometric Distribution Type	Flood	Energy Certifications	DLC Standard cETLus
Mounting	NPT/NPS Ground / Floor Wall	IP Rating	IP65 [Dust penetration-protected, jet-proof]
Number Of Pieces	1	Vibration Rating	1.5G
Grade	Value Grade	Initial performance (IEC compliant)	
Operating and electrical		Luminaire Lumens	3256
Voltages	120/208/240/277 V	Efficacy	115 lm/W
Luminaire Input Watts	28	Application conditions	
Conduit Connection	7/8 inch knockout	Ambient temperature range	-40 °C to 40 °C
Mechanical and housing		Max Ambient Temp	40 °C
Shape	Rectangular		

Slim Flood LED (TF)

Min Ambient Temp	-40 °C
Min Ambient Temp-DUP(do not use)	-40 °C
Product data	
Full product code	911401733572
Order product name	TF30-NW-G1-K-FL-8-BZ
EAN/UPC - Product	783352025951
Order code	TF30-NW-G1-K-FL-8-BZ
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	911401733572
Net Weight (Piece)	0.980 kg
Catalog Number	TF30-NW-G1-K-FL-8-BZ
Catalog Number Description	Slim Flood, 30W, 4000K, Generation 1, Knuckle mount, 120-277VAC, Bronze finish

