

# Straight Blade Devices

15 and 20 Ampere, 125 Volts

**IP20**  
SUITABILITY



15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP



20A 125V  
NEMA 5-20R  
UL CSA  
1 HP

## EdgeConnect™ Hubbell-PRO Extra Heavy Duty Specification Grade Receptacles

Finder Groove face, duplex, spring termination

Black	<b>5262STBK</b>	<b>5362STBK</b>
Blue	<b>5262STBL</b>	<b>5362STBL</b>
Brown	<b>5262ST</b>	<b>5362ST</b>
Gray	<b>5262STGY</b>	<b>5362STGY</b>
Green	<b>5262STGN</b>	<b>5362STGN</b>
Ivory	<b>5262STI</b>	<b>5362STI</b>
Light Almond	<b>5262STLA</b>	<b>5362STLA</b>
Orange	<b>5262STO</b>	<b>5362STO</b>
Red	<b>5262STR</b>	<b>5362STR</b>
White	<b>5262STW</b>	<b>5362STW</b>



5362STI

Tamper-Resistant, smooth face, duplex, spring termination



Black	<b>5262STBKTR</b>	<b>5362STBKTR</b>
Blue	<b>5262STBLTR</b>	<b>5362STBLTR</b>
Brown	<b>5262STTR</b>	<b>5362STTR</b>
Gray	<b>5262STGYTR</b>	<b>5362STGYTR</b>
Green	<b>5262STGNTR</b>	<b>5362STGNTR</b>
Ivory	<b>5262STITR</b>	<b>5362STITR</b>
Light Almond	<b>5262STLATR</b>	<b>5362STLATR</b>
Orange	<b>5262STOTR</b>	<b>5362STOTR</b>
Red	<b>5262STRTR</b>	<b>5362STRTR</b>
White	<b>5262STWTR</b>	<b>5362STWTR</b>



5362STWTR

## EdgeConnect™ Commercial Specification Grade Receptacles

### Duplex

Smooth face, duplex, spring termination

Color	Catalog Number	
Black	<b>BR15STBK</b>	<b>BR20STBK</b>
Blue	<b>BR15STBL</b>	<b>BR20STBL</b>
Brown	<b>BR15ST</b>	<b>BR20ST</b>
Gray	<b>BR15STGY</b>	<b>BR20STGY</b>
Green	<b>BR15STGN</b>	<b>BR20STGN</b>
Ivory	<b>BR15STI</b>	<b>BR20STI</b>
Light Almond	<b>BR15STLA</b>	<b>BR20STLA</b>
Orange	<b>BR15STO</b>	<b>BR20STO</b>
Red	<b>BR15STR</b>	<b>BR20STR</b>
White	<b>BR15STW</b>	<b>BR20STW</b>



BR20STGY

Tamper-Resistant, smooth face, duplex, spring termination



Black	<b>BR15STBKTR</b>	<b>BR20STBKTR</b>
Blue	<b>BR15STBLTR</b>	<b>BR20STBLTR</b>
Brown	<b>BR15STTR</b>	<b>BR20STTR</b>
Gray	<b>BR15STGYTR</b>	<b>BR20STGYTR</b>
Green	<b>BR15STGNTR</b>	<b>BR20STGNTR</b>
Ivory	<b>BR15STITR</b>	<b>BR20STITR</b>
Light Almond	<b>BR15STLATR</b>	<b>BR20STLATR</b>
Orange	<b>BR15STOTR</b>	<b>BR20STOTR</b>
Red	<b>BR15STRTR</b>	<b>BR20STRTR</b>
White	<b>BR15STWTR</b>	<b>BR20STWTR</b>



BR20STWTR

## EdgeConnect™ Style Line® Decorator\*

Style Line® decorator duplex, spring termination

Black	<b>DR15STBK</b>	<b>DR20STBK</b>
Blue	<b>DR15STBL</b>	<b>DR20STBL</b>
Brown	<b>DR15ST</b>	<b>DR20ST</b>
Gray	<b>DR15STGY</b>	<b>DR20STGY</b>
Green	<b>DR15STGN</b>	<b>DR20STGN</b>
Ivory	<b>DR15STI</b>	<b>DR20STI</b>
Light Almond	<b>DR15STLA</b>	<b>DR20STLA</b>
Orange	<b>DR15STO</b>	<b>DR20STO</b>
Red	<b>DR15STR</b>	<b>DR20STR</b>
White	<b>DR15STW</b>	<b>DR20STW</b>



DR20STW

Tamper-Resistant, Style Line® decorator duplex, spring termination



Black	<b>DR15STBKTR</b>	<b>DR20STBKTR</b>
Blue	<b>DR15STBLTR</b>	<b>DR20STBLTR</b>
Brown	<b>DR15STTR</b>	<b>DR20STTR</b>
Gray	<b>DR15STGYTR</b>	<b>DR20STGYTR</b>
Green	<b>DR15STGNTR</b>	<b>DR20STGNTR</b>
Ivory	<b>DR15STITR</b>	<b>DR20STITR</b>
Light Almond	<b>DR15STLATR</b>	<b>DR20STLATR</b>
Orange	<b>DR15STOTR</b>	<b>DR20STOTR</b>
Red	<b>DR15STRTR</b>	<b>DR20STRTR</b>
White	<b>DR15STWTR</b>	<b>DR20STWTR</b>