

## Flush Round Single or Multi-Service Non-Metallic Floor Boxes, for Use In Concrete Floors

<b>Min. Depth of Pour</b>	3.00" (76.2)
<b>Cubic Inch (cm<sup>3</sup>) Capacity</b>	100 cu. in. (1638.7 cm <sup>3</sup> ) prior to cutting level to floor (19.5 cu. in. (313.2 cm <sup>3</sup> ) per inch of depth).
<b>Dimensions – A</b>	6.00" (152.4)
<b>Dimensions – B</b>	7.08" (179.8)
<b>Dimensions – C</b>	6.69" (169.9)
<b>Dimensions – D</b>	5.38" (136.5)
<b>Hubs</b>	(2) 1" and (2) 3/4" Conduit Hubs
<b>Concrete Cover Included</b>	✓
<b>Closure/Reducer Plugs</b>	(2) 1" plugs close off 1" hubs or reduce 1" to 3/4" (2) 3/4" plugs close off 3/4" hubs or reduce 3/4" to 1/2"

Description	Catalog Number
<b>Adapter</b> Required for all applications.	<b>PFBA1A</b>
<b>Low Voltage Divider</b> Required for use with catalog number PFB1 when used in multi-service applications. Accepts Hubbell standard duplex receptacles or 15A Twist-Lock® duplex receptacles (HBL4700 series).	<b>PFBT1A</b>
<b>"Y" Adapter</b> 3/4 in. "Y" adapter to feed parallel runs of 3/4 in. conduit.	<b>PFBYA1</b>
Pre-pour PVC stand increases PFB1 box height 2.5 in. to 4.0 in. within the concrete pour.	<b>PFBSTAND</b>

Note: UL File Number E92074. CSA File Number LR18416.

### Flush Round Covers and Flanges<sup>†</sup>

**Multi-Service Cover and Flange Assemblies**  
Includes floor box cover with duplex flaps, (2) 1/2 in. dia. low voltage feed through holes and matching carpet flange. 6.25 in. Diameter

SF39253A	PFBCBRA	PFBCBLA	PFBCGYA	PFBCIA
Brass	Brown Non-Metallic	Black Non-Metallic	Gray Non-Metallic	Ivory Non-Metallic

### Metal Carpet Flange

Use with single service covers for carpet applications. 6.25 in. Diameter

S3082	SA3082
Brass	Brushed Aluminum

### Adapter Ring

Use with single service covers for tile applications.

S5016	SA5016
Brass	Aluminum

### Multi-Service Replacement Covers

Material	Metallic	Color	Non-metallic
Solid Brass	<b>BRS2RCA</b>	Black Brown Gray Ivory	<b>PFBRCBLA</b> <b>PFBRCBRA</b> <b>PFBRGGA</b> <b>PFBRCIA</b>

### Single Service Covers<sup>†</sup>

Brass	S3925	S3725	S2525	S2725	S2925	S3525	S3325	S3913
Aluminum	SA3925	SA3725	SA2525	SA2725	SA2925	—	—	SA3913
3.88 in. Dia.								
	Duplex Flap	Duplex Screw	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle	2 3/8" Single Receptacle	2 1/8" Single Receptacle (Terrazzo Floor)	Blank

### One Piece Brass Cover and Carpet Flange<sup>†</sup>

Brass	SF3925*	SFB3926**	SF2525*	SF2725*	SF2925*
Aluminum	SFA3925*	SFA3926	—	—	—
6.25 in. Dia.					
	Duplex Flap	Style Line® Decorator Opening	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle

\*Note: Adapter ring S5016 is required for mounting SF series covers onto PFBA1A.

\*\*Note: brass plated aluminum

### Furniture Feed Plate

Unpainted plate with 1 in. threaded opening.	PFBP1
	Steel

<sup>†</sup>COVER LOAD RATING; Metallic covers and flanges 2,000 lbs. with 2x safety factor, Non-metallic covers and flanges 300 lbs. Load applied through a 3 in. (76) mandrel at the center of the cover.