

4-IN. LOW VOLTAGE RECESSED PROGRAM

low voltage 12V

4-Inch Low Voltage Housings



GR-HR03
4" New Construction Housing with magnetic transformer.

Features

- Transformer located between junction box and housing for ease of access when servicing
- Transformer pre-installed on junction box
- Thermally protected to prevent over heating
- Commercial sized junction box
- For use with MR16 lamps 50W max., 12V
- Comes with quick connect push-in terminals
- Heavy duty hanger bars can be adjusted to fit up to a 24" joist construction
- Can be installed in suspended ceilings



GR-HR04
4" Remodel Housing with magnetic transformer

Features

- 4-knock out holes
- Thermally protected to prevent over heating.
- For use with MR16 lamps 50W max., 12V
- Low voltage MR16 bulbs provide brighter, whiter light with one third more light per watt than conventional bulb.



GR-HR06
4" Housing for Insulated Ceilings, airtight, with magnetic transformer

Features

- Thermally protected to prevent over heating.
- For use with MR16 lamps 50W max., 12V
- Low voltage MR16 bulbs provide brighter, whiter light with one third more light per watt than conventional bulb.
- Fits up to 24" joist construction.
- Airtight housing prevents air flow between attic and living areas.
- Quick push-in connectors
- Can be installed in suspended ceilings



Applications

- New Construction, Remodel and I.C applications
- Insulated or non insulated ceilings
- T-Bar ceilings

VBE-1
Vapour Barrier Extender



Features

- Constructed of PVC, Rated for 90°C
- Flat flange all around to allow for better fit to joist
- Help control moisture in these areas: Ceilings, Basements crawl spaces, floors slab-on-grade foundations, and walls

Features & Benefits of 4-inch Trims

- **Cones/Baffles:** Airtight, Baffles and Reflectors
- **Shower:** Fresnel, Dropped Albalite or Opal glass with Neoprene gaskets
- **Gimbles:** 35° angular adjustment



Lamps (Low Voltage)

- MR16, 50W max.



4-IN. LOW VOLTAGE RECESSED PROGRAM

low voltage **12V**

4-Inch Low Voltage Housings



GR-HR03-75

4" New Construction Housing
with magnetic transformer

Features

- Fits up to 24" joist construction
- Can be installed in suspended ceilings
- Thermally protected to prevent over heating
- For use with MR16 lamps 75W max., 12V
- Low voltage MR16 bulbs provide brighter, whiter light with one third more light per watt than conventional bulb
- New Construction housing has adjustable mounting brackets with captive nails



GR-HR04-75

4" Remodel Housing with
magnetic transformer

Features

- 4-knock out holes
- Thermally protected to prevent over heating
- For use with MR16 lamps 75W max., 12V
- Low voltage MR16 bulbs provide brighter, whiter light with one third more light per watt than conventional bulb



Applications

- **New Construction, Remodel applications**
- **T-Bar Ceilings**

Features & Benefits of 4-inch Trims

- **Cones/Baffles:** Airtight, Baffles and Reflectors
- **Shower:** Fresnel, Dropped Albalite or Opal glass with Neoprene gaskets
- **Gimbles:** 35° angular adjustment



Lamps (Low Voltage)

- **MR16, 75W max.**



4-IN. LOW VOLTAGE RECESSED PROGRAM

low voltage 12V

4-Inch Low Voltage Housing



GR-HR04C2-RM

4" Remodel Housing with magnetic transformer equipped with screw down clamp

Features

- Thermally protected to prevent over heating
- For use with MR16 lamps 50W max., 12V
- Comes with push-in terminals for easy wiring
- Two extra terminals available for branch wiring
- Can be converted to a New Construction housing with a 4-in pre-mounting plate (#P-4000)



Applications

- Remodel applications
- T-Bar Ceilings



Features

- For use with screw down "C" style remodel housing only

P-4000

4" New Construction pre-mounting plate for use with GR-HR04C2-RM remodel housings

Features & Benefits of 4-inch Trims

- **Cones/Baffles:** Airtight, Baffles and Reflectors
- **Shower:** Fresnel, Dropped Albalite or Opal glass with Neoprene gaskets
- **Gimbles:** 35° angular adjustment

Lamps (Low Voltage)

- MR16, 50W max.



LITELINE CORPORATION, Brampton, Ontario, Canada L6T 5B7

Phone: 416-996-1856 • Fax: 905-654-8990/1-888-738-9736 • Email: sales@liteline.com • Website: www.liteline.com

Toll free technical support: 1-866-730-7704

rev. 01.14.08



4-IN. LOW VOLTAGE RECESSED PROGRAM

HOUSINGS



PART NO.	DESCRIPTION	UPC	CASE QTY
GR-HR03	4" New Construction Housing with magnetic transformer. Use with MR16 lamp, 50W max.	7-71250-30156-7	6



GR-HR03-75	4" New Construction Housing with magnetic transformer. Use with MR16 lamp, 75W max.	7-71250-91279-4	6
------------	---	-----------------	---



GR-HR04	4" Remodel Housing with magnetic transformer. Use with MR16.lamp, 50W max.	7-71250-30147-5	6
---------	--	-----------------	---



GR-HR04C2-RM	4" Remodel Housing with magnetic transformer equipped with screw down clamp. Use with MR16 lamp, 50W max.	7-71250-90606-9	6
--------------	---	-----------------	---



GR-HR04-75	4" Remodel Housing with magnetic transformer Use with MR16 lamp, 75W max.	7-71250-91277-0	6
------------	---	-----------------	---



GR-HR06	4" Housing for Insulated Ceilings with magnetic transformer, air tight. Used with MR16 lamp, 50W max.	7-71250-90605-2	6
---------	---	-----------------	---

TRIMS



PART NO.	DESCRIPTION	UPC	CASE QTY	
GR-TH01-BK	Round stepped baffle with white trim ring	Black	7-71250-30103-1	6
GR-TH01-WH	For use with MR16 75W lamps	White	7-71250-30104-8	



GR-TH02-G	Round specular baffle.	Gold	7-71250-30106-2	6
GR-TH02-S	For use with MR16 75W lamps.	Silver	7-71250-30105-5	



GR-TH03	Adjustable slot aperture (White) For use with MR16 75W lamps	White	7-71250-30107-9	6
---------	---	-------	-----------------	---



GR-TH04-BK	Eyeball baffle.	Black	7-71250-30108-6	6
GR-TH04-WH	For use with MR16 50W lamps	White	7-71250-30146-8	



GR-TH05-BK	Narrow beam black pinhole baffle.	Black	7-71250-30109-3	6
GR-TH05-WH	For use with MR16 50W lamp	White	7-71250-91278-7	










GR-TH18-NB-AB	Tilting round front load gimble.	Antique Brass	7-71250-91114-8	6
GR-TH18-NB-BB	For use with MR16 75W lamps	Brushed Brass	7-71250-91118-6	
GR-TH18-NB-BK		Black	7-71250-91110-0	
GR-TH18-NB-BN		Brushed Nickel	7-71250-91116-2	
GR-TH18-NB-WH		White	7-71250-91112-4	





4-IN. LOW VOLTAGE RECESSED PROGRAM

TRIMS

PART NO.	DESCRIPTION		UPC	CASE QTY.	
	GR-TH18R-AB	Tilting round front load gimble. For use with MR16 75W lamps	Antique Brass	7-71250-91279-4	6
	GR-TH18R-BK		Black	7-71250-91044-8	
	GR-TH18R-BN		Brushed Nickel	7-71250-91271-8	
	GR-TH18R-STS		Stainless Steel	7-71250-91285-5	
	GR-TH18R-WH		White	7-71250-91045-5	
	GR-TH18R3-AB	Tilting round front load gimble. For use with MR16 75W lamps	Antique Brass	7-71250-91591-7	6
	GR-TH18R3-BK		Black	7-71250-91592-4	
	GR-TH18R3-BN		Brushed Nickel	7-71250-91685-3	
	GR-TH18R3-MIV		Matte Ivory	7-71250-91191-9	
	GR-TH18R3-STS		Stainless		
GR-TH18R3-WH	White				
	GR-TH19-WH	Egress / Regress rotating down light or Wall Washer. For use with MR16 50 W lamps	White	7-71250-90072-2	6
	GR-TH313-MIV	Tilting round Matte Ivory gimble. For use with MR16 50W lamps.	Matte Ivory	7-71250-91046-2	6
	HV4-TH4013-BN	White shower trim with Frosted Glass lens and neoprene gasket. For use with MR16, 35W lamp	Brushed Nickel	7-71250-91724-9	6
	HV4-TH4013-WH		White	7-71250-90610-6	
	HV4-TH4019-WH	White shower trim with Frosted Glass lens and neoprene gasket. For use with MR16 35W lamps	White	7-71250-91150-6	6
	GR-TH24-BK	Metal retractable trim. For use with MR16 75W lamps and Low Voltage 4" housings only.	Black	7-71250-91280-0	6
	GR-TH24-BN		Brushed Nickel	7-71250-90614-4	
	GR-TH24-CH		Chrome	7-71250-91281-7	
	GR-TH24-PB		Polished Brass	7-71250-30144-4	
	GR-TH24-WH		White	7-71250-30143-7	

ACCESSORIES

PART NO.	DESCRIPTION		UPC	CASE QTY.
	VBE-1	Vapour Barrier Extender, for use with all Liteline recessed IC fixtures to prevent moisture from entering into the attic. Material rated to 90° C	7-71250-90494-2	6
	P-4000	4" New construction premounting plate. For use with GR-HR04C20-RM remodel housings.	7-71250-90607-6	24