



## T5250-B

15 Amp Recessed Single Tamper-Resistant Outlet/Receptacle, Brass

Single Receptacle Outlet, Commercial Specification Grade, Recessed Display, Tamper-Resistant, Smooth Face, 15 Amp, 125 Volt, Back or Side Wire, NEMA 5-15R, 2-Pole, 3-Wire - Brass

- Tamper-Resistant receptacle meets NEC Article 406.12 requirements
- Single receptacle is ideal for applications that require a dedicated circuit
- Quick installation: simply wire and mount to a standard single gang box

UPC Code : 078477703496

Country Of Origin : Mexico

NEMA :  5-15R

### Technical Information

#### AC Horsepower Ratings

**At Rated Voltage** : 1/2 HP

#### Electrical Specifications

**Amperage** : 15 A

**Dielectric Voltage** :  
Withstands 2000V per UL498

**Pole** : 2

**Temperature Rise** : Max 30C  
after 100 cycles OL at 150  
percent rated current

**Voltage** : 125 VAC

**Wire** : 3

#### Environmental Specifications

**Operating Temperature** : -40°  
C to 75°C

#### Material Specifications

**Body Material** : Nylon

**Cap Material** : Brass

**Face Material** : Nylon

**Grounding Screw** : Steel

**Line Contacts** : Brass Triple-  
Wipe

**Mounting Screws** : Steel

**Strap Material** : Zinc-Plated  
Steel

**Wallplate** : Solid Brass 0.060  
In Thick

#### Mechanical Specifications

**Terminal Accom.** : 14-10 AWG

**Terminal ID** : Brass-Hot,  
Green-Ground, Silver-Neutral

**Termination** : Back and Side  
Wire

#### Product Features

**Color** : Ivory

**Feature** : Tamper-Resistant

**NEMA** : 5-15R

**Type** : Wood Frame

Standards and Certifications

Warranty

**ANSI : C-73**

**Warranty : 10-Year Limited**

**Applicable Standards : UL**  
498, UL514A, CSA C22.2 No.  
42, CSA C22.2 No 18.1-04

**Certification/Listing :**  
cCSAus, NOM-ANCE

**NEMA : WD-1 & WD-6**

**SPECIFICATION SUBMITTAL**

<b>JOB NAME:</b> <input type="text"/>	<b>CATALOG NUMBERS:</b> <input type="text"/>	
<b>JOB NUMBER:</b> <input type="text"/>	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc**

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.

T. Monday-Friday): +1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)

5386- 1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2024 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts](http://www.leviton.com/international/contacts)

**© 2024 Leviton Manufacturing Co., Inc.**