

Vapor Barrier Cable Box 1-Gang, Non-Metallic

By TradeSelect
Catalog # [2011FBAR](#)

Vapor Barrier Cable Box 1-Gang, Non-Metallic, 2-3/4 in Deep,
1/2 in Setback



Features

- Self-clamping wire entry clamps
- Vapor/air barrier flange and integral wire entry seal provides superior energy savings and quick installation
- Hands free installation for 1/2 in., 5/8 in., or 3/4 in. drywall

Application

- Vapor barrier boxes prevent unwanted penetration of exterior air and help maintain the existing interior environment from elements outside the structure
- RACO® nonmetallic vapor barrier cable boxes provide the installer with a cost alternative that is lightweight and easy to install and provide excellent protection for wiring system or devices
- RACO® nonmetallic cable boxes are used in branch circuit wiring to splice wires and accommodates wiring devices such as switches and receptacle

General

Bracket Setback	0.50
Cable Clamps	4
Material	Thermoplastic Resin
UPC	805035000212
Volume	18
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	2.8125 in
Cubic Capacity	46.10546875 cu.in
Depth	2.8125 in
Height	3.625 in
Weight	0.256 lb
Width	3.625 in

Certifications and Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	50
Pallet Quantity	1200

Product Assets

[3D Product View](#)
[Brochures - H3672 Banana Boxes](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)

